

PASSIVE-DI0° PLASTIC,6XM12.4POL,PRE-WIRED CABLE

3.0m PUR-JB 6*0,34+3*0,75

6-way, 4-pole

PUR/PVC


3.0 m

with LED for digital PNP-signals 24 V DC


Further cable lengths on request.

[Link to Product](#)**Illustration**

M12 Females 4-pole



stay connected



Product may differ from Image

Approvals



Technical Data

| | |
|-------------------------------|-------------------------------|
| Operating voltage | 24 V DC |
| Operating voltage indicator | LED (green) |
| Signal per port | 1 - (31-32) |
| LED display per port | LED (yellow) per signal (PNP) |
| Operating current per contact | max. 4 A |
| Total current | max. 8 A |
| Locking of ports | Screw thread M12 × 1 mm |

Cables

| | |
|-----------------------|---------------------------------|
| No./diameter of wires | 6×0.34 + 3×0.75 mm ² |
| C-track properties | 2 Mio. |
| Material (jacket) | PUR/PVC |
| Outer diameter | approx. 9.1 mm |
| Bend radius (moving) | 12 × outer Ø |
| Cable number | 355 |

General data

| | |
|----------------------|----------------------------------------|
| Protection | IP67 inserted and tightened (EN 60529) |
| Dimensions H × W × D | 100.5×54.5×25 mm |
| Temperature range | -20...+80 °C |

Contact layout

| | |
|-----------|-----------|
| Contact 1 | (+) |
| Contact 2 | (NC)/(S2) |
| Contact 3 | (-) |
| Contact 4 | (NO)/(S1) |

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

Murrelektronik GmbH | Falkenstraße 3, 71570 Oppenweiler | Fon +49 (71 91) 47-0, Fax +49 (71 91) 47-491000 | shop@murrelektronik.de | shop.murrelektronik.de

Contact 5 (Earth)

Commercial data

| | |
|------------------------|----------|
| country of origin | CZ |
| customs tariff number | 85444290 |
| minimum order quantity | 1 |