


LED-INDICATOR GREEN


LED 10mm - 24V DC - 20 mA - IP67

(green)
24 V DC

[Link to Product](#)

Illustration





Product may differ from Image

Technical Data

Operating voltage	24 V DC $\pm 15\%$
Current consumption	approx. 15 mA
Protection acc. to (IEC 60529/EN 60529)	IP67

General data

Housing	Brass, chrome plated
LED \varnothing	10 mm
Front panel hole diameter \varnothing	14 mm
Dimensions H x W x D	16x16x45 mm
Temperature range	-40...+70 °C
Connection	Faston 2.8 x 0.8 mm

Commercial data

country of origin	DE
customs tariff number	85414010
minimum order quantity	10