

Ultrasonic transit time Sensor Clamp-On, Uni, Very-Hi-Temp. Size 4A, pair, dedicated, Ex Zone 0,1,2, Class 1, Div 1,2, any pipe materials, Liquid, Pipe Diameter range 400 - 1200 mm (16 -47"), Temperature -40C - +230C (-40F - +446F) Housing Stainless Steel corrosion resistant, for FST020, FST030, (substitute for FUx1010)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.de/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com>