


# USB 2.0 Cable

## Type A Plug to Micro Type B Plug



### Diagram



### Note:

- Cable Spec: 28AWG (7×0.12Cu)×1P+28AWG (7/0.12Cu)×2C+AD(7/0.12CCAM)+Braid(16×3/0.12ALMG)  
 Jacket Material: PVC OD: 3.8 ±0.15mm  
 Cable Colour: Black  
 Cable Printing: USB 2.0 cable fully rated 80°C 30V
- Connector A: USB A Male Solder Type USB 2.0 Compliant  
 Insulation: White  
 Contacts: Gold Plated  
 Shell: Nickel Plated
- Connector B: Micro USB B Male Solder Type  
 Insulation: Black  
 Contacts: Gold Plated  
 Shell: Nickel Plated
- Over Mold Colour: PVC-Black
- Parameter Settings: CT-8681FA  
 Conductive Resistance: 3Ω (Max.)  
 Insulated Resistance: 5MΩ (Min.)
- 100% electrical performance test

### Part Number Table

Description	Part Number
USB 2.0 Cable, Type A Plug to Micro Type B Plug, 3ft, Black	83-16412