

Product information

49 41 A21

Precision Circlip Pliers

For external circlips on shafts

DIN 5254 B



MM  90°



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Heavy duty under continuous use; up to 10 times longer service life
- Precise, smoothly-operating screw joint
- Forged
- Large contact faces on the tips: no distortion of circlips, easy fitting
- Slim head style allows use in confined areas
- Internal opening spring, protected and captive
- Handles with non-slip plastic coating
- DIN 5254 B; 90° angled tips
- With overstretching limiter for standardised assembly in accordance with DIN 471
- The adjustable stop screw prevents the rings from overstretching
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

General

Article No.	49 41 A21
EAN	4003773079613
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	169 g
Dimensions	165 x 36 x 13 mm
Standard	DIN 5254 B
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Size of shaft	Ø 19 – 60 mm
Tips (diameter)	1.8 mm

technical change and errors excepted



Spring inside the joint: the spring is protected inside the precisely bolted joint. It does not hinder work and cannot get dirty or lost.