

Product information

86 01 250

Pliers Wrench

Pliers and a wrench in a single tool



- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings - working directly on chrome!
- With scaling for presetting the width apart from the workpiece
- Adjustable tightening tool
- Also excellent for gripping, holding, pressing and bending workpieces
- Push the button for adjustment on the workpiece
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- Reliable catching of the hinge bolt: no unintentional shifting
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened




General

Article No.	86 01 250
EAN	4003773082385
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
Weight	465 g
Dimensions	250 x 52 x 17 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw thickness (joint) (B2)	8.0 mm
Joint thickness (B3)	14.0 mm
Tips thickness (B1)	8.0 mm
Adjustment positions	19
Capacities for nuts	Ø 2 Inch
Capacities for nuts	52 mm



technical change and errors excepted



Opening width lasered onto the pliers head (metric on the front and imperial on the back)