



Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 10M ohm Min.
4. Hi-Pot: 300VDC/10ms.



Pin Assignment



⑧	A0020100-00173	USB TYPE C~n Back Nickel Plated Shell	1	pcs	版本	ECN编号	描述	日期	变更人	
⑦	A0020100-00172	USB TYPE C~n Front Nickel Plated Shell~	1	pcs						
⑥	A10-R075552	H.S TUBE Color:Black Ø:1.0 L=16mm*1pcs	0.016	M	TOLERANCE INCHES M/M	. X .015 .30	. XX .010 .10	. XXX .005 .05	TITLE: USB2.0 CM TO AF CABLE L=1M	
⑤	A5-R047001	45P PVC Color:Sonw BLACK	16	g						
④	A5-R047011	Transparent PE	6	g						
③	B010-00880	USB 2.0 C Type Black Insulation Nickel Plated Shell With PCBA(Resistance10KΩ)	1	pcs	DRAWN BY	李敏	CUSTOMER :		CPC	
②	A2-R029145	USB2.0 AF White Insulation Solder G/F Plated Terminal no edge Take to mould	1	pcs			CUSTOMER P/N :		CS28711	
①	A4-R005013	NO-UL 30AWG (19/0.06TC)*2C+24AWG (26/0.1TC+250Dnylon)*1C+3E (19/0.05TC+250Dnylon)+AB (16/9/0.06TC 95%TC) OD:3.0MM PVC black no mark	0.98	M	CHECK BY		SCALE	NONE	DRAWING NO. :	REV. A
NO		DESCRIPTION	Q'TY	UNIT	APPD BY		UNIT	mm		C06026-00004
							DATE	2015.05.13		