

T50ML9C2



Article Number: 113-05419

Screw Mount Tie, 50lb, 15.4", Max Bundle Diameter 4.0", #10 Screw, PA66HS, Natural, 100/pkg



Download spec sheet

Base Data

Local Order Number	T50ML9C2
Type	T50ML
Color	Natural (NA)
Features and Benefits	<ul style="list-style-type: none"> • Mount design secures firmly with any #10 Screw. • Screw mount style creates low insertion and high extraction force.
Product Description	Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.
Short Description	Screw Mount Tie, 50lb, 15.4", Max Bundle Diameter 4.0", #10 Screw, PA66HS, Natural, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225 N
Length L (Imperial)	15.4 "
Length L (Metric)	390.0 mm
Fixation Method	fixing hole
Identification Plate Position	none
Mounting Screw Type	M5
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18 "
Width W (Metric)	4.7 mm
Height H (Imperial)	0.23 "
Height H (Metric)	5.7 mm
Bundle Diameter Min. (Imperial)	0.12 "
Bundle Diameter Min. (Metric)	3.0 mm
Bundle Diameter Max. (Imperial)	4.0 "
Bundle Diameter Max. (Metric)	100.0 mm
Mounting Hole Diameter D (Imperial)	0.22 "
Mounting Hole Diameter D (Metric)	5.5 mm
Thickness T (Imperial)	0.05 "
Cable Tie Head Length (Imperial)	0.79 "
Cable Tie Head Width (Imperial)	0.35 "
Mounting Hole Diameter D Max.	5.5 mm

(Metric) Mounting Hole Diameter D Min. (Metric) 5.5 mm

Thickness T (Metric) 1.2 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100 Pieces

Carton Quantity 5000

Weight (Metric) 2.9 kg

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes

Certification/Specification UL

UL Listed (US and Canada) Yes

UL Recognized (US and Canada) Yes