


## Myriad Deco IP65 Chrome Bezel

MYRIAD DECO IP65 FLOOD 3000K DALI BLACK CBEZ  
2058969



### Product features

- MYRD IP FL 3K DALI BLK CBEZ



## PRODUCT OVERVIEW

Product name	MYRIAD DECO IP65 FLOOD 3000K DALI BLACK CBEZ
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	988
Luminaire efficacy (lm/W)	99
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	46
Photobiological Risk Group	RG1
Total power consumption (W)	10
Electrical protection	Class II
Control gear type	Electronic ballast
Dimming method	DALI
Minimum dimming level (%)	1
Housing colour	Black
IP rating	IP65/20
IK rating	IK02
Product EAN number	5025768589692

## DATA TABLE

### General data

Product name	MYRIAD DECO IP65 FLOOD 3000K DALI BLACK CBEZ
Technology	LED

## Myriad Deco IP65 Chrome Bezel

*MYRIAD DECO IP65 FLOOD 3000K DALI BLACK CBEZ*  
2058969

Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	988
Luminaire efficacy (lm/W)	99
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	46
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	10
Mains voltage (V)	230-240V
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

### Physical data


Housing colour	Black
IP rating	IP65/20
IK rating	IK02
Diffuser finish	Bezel (or Ring)
Nominal Product Height (mm)	72
Nominal Product Diameter (mm)	90
Cutout Dimensions (W x L in mm or Diameter in mm)	76
Weight (kg)	0.44
Recessed Depth (mm)	72

## Myriad Deco IP65 Chrome Bezel MYRIAD DECO IP65 FLOOD 3000K DALI BLACK CBEZ 2058969

### Packaging

Single packaging type	Carton
Product EAN number	5025768589692
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768589692
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

### PHOTOMETRY



Distance [m]	Cone diameter [m]	E <sub>0</sub> [lx]	E <sub>1</sub> [lx]	E <sub>2</sub> [lx]
0.5	0.34	788	18.9°	3289
1.0	0.68	193	18.9°	817
1.5	1.03	85	18.9°	333
2.0	1.37	48	18.9°	204
2.5	1.71	30	18.9°	131
3.0	2.05	21	18.9°	91

Distance [m] Cone diameter [m] Illuminance [lx]  
C0 - C180 (Half beam angle: 37.9°)

### TECHNICAL DRAWINGS

