

Cutting body solid carbide TiAlN for Top Drill M 1

For universal use up to 1300 N/mm²



Application:

High-performance drilling in conjunction with indexable insert drill for universal application up to 1300 N/mm²

Execution:

- Precision-ground indexable insert, tip angle 140°

Advantage:

- Simply replacement of cutting body: No screws or clamps required
- The cutting body can be replaced using a wrench, which is supplied with each tool body
- No regrinding costs
- Consistent performance from cutting edge to cutting edge



Art. no.	11224 146
Brand	WIDIA
Manufacturer Part Number	3849092
Cutting material	SC
Carbide type	WU25PD
Cutting edge diameter	14.6 mm
Indexable insert type	W23
Surface	TiAlN
Cutting direction	Right-hand cutting
Angle of the tip	140 Degree
Gross Weight	0.007 kg
Product Group	1XA

EAN

4021169583582