

Adjustable crocodile clamp

With counter-holder



Application:


The crocodile is used with all clamping tasks where clamping is achieved using T-grooves and tapped holes.

Execution:

- Tempered and galvanised
- Variable and quick adjustment
- The captive thrust piece and counter-holder are connected to the adjustable clamp (cannot be lost).
- Particularly suitable for use on injection moulding machines and presses
- Accessories facilitate variable adjustment of the clamping height
- Infinitely variable adjustment of clamping height

Advantage:

- Captive thrust piece connected to the adjustable clamp (cannot be lost), crocodile can therefore be used quickly and flexibly
- Heights are quickly overcome and packing the underside of the adjustable clamp does not present a problem
- Accessories facilitate variable adjustment of the clamping height



Art. no.	26224 020
Brand	AMF
Manufacturer Part Number	79798
Size	2
Suitable T-groove width	12 mm, 14 mm, 16 mm, 18 mm
Tension force	40 kN
Min./max. adjustment range	0-70 mm
Length	150 mm
Width	55 mm
Height	36 mm
Thickness	21 mm
Bore diameter	17 mm
Gross Weight	1.492 kg
Product Group	260

EAN

4020772079796