

Platform trolley series 500 with 2 front walls, zinc plated

Loading area made of MDF board, load capacity 500 kg



Execution:

- Galvanised
- Loading area, longitudinal walls 400 mm high, made of melamine-coated MDF board
- Loading area height 260 mm
- Push handle made of 25 mm steel tubing
- 2 fixed castors and 2 castors made of solid rubber 200 x 50 mm
- The 500 series also includes table trolleys, cabinet trolleys, platform trolleys with front walls and other variants.



Art. no.	50250 024
Brand	KONGAMEK
Manufacturer Part Number	KM533-3
Type	With front and rear wall
Load-carrying capacity	500 kg
Length	1200 mm
Width	800 mm
Height	900 mm
Loading surface length	1200 mm
Loading surface size	1200 x 800 mm
Loading-surface width	800 mm
Material of loading surface	Medium density fibreboard
Colour	Silver coloured
Surface	Zinc plated
Number of steering rollers	2
Number of fixed rollers	2
With wheel lock	No
Wheel diameter	200 mm
Material of wheel	Solid rubber
Made in	Sweden
Gross Weight	36.000 kg
Product Group	5AT

EAN

7350050352110