

## LED lamp socket E14

Matt or clear, dimmable or non-dimmable

### Execution:

- Screw socket E14
- High-quality lamp with a very long service life of min. 15,000 hours
- Light colour temperature 2700 K
- Ra value 80, energy efficiency class A+ or A++
- Candle-shaped light fixture in matt or clear glass

<b>Art. no.</b>	<b>56887 210</b>
<b>Dimmable</b>	No
<b>Luminous flux</b>	470
<b>Power rating</b>	5.5
<b>Gross Weight</b>	0.040 kg
<b>Product Group</b>	5IH

