

BSW 903 pneumatic countersink drill bit

Angled design

MANNESMANN
DEMAG

Application:

For deburring difficult to access areas, such as holes with cross-drilled bores

Execution:

- Angled design
- Thermally insulated handle
- With speed control

Advantage:

- Extremely quiet and robust
- Easy handling, especially for large workpieces
- Low air consumption, as drive is only applied during the work process



Art. no.	75061 250
Brand	MANNESMANN DEMAG
Manufacturer Part Number	60012085
Model	BSW 903
Valve design	Lever valve
Max. idle speed	900 rpm
Power input	35 W
Air consumption	2.8 l/s
Suitable for bore diameter	10 mm
Length	258 mm
Head height	18 mm
Diameter of housing	25 mm
Weight	0.4 kg
Max. bore diameter	10 mm
Connection thread	G 1/4 inch
With speed control	Yes
Sound-pressure level	68 dB
Gross Weight	1.067 kg
Product Group	7AA

EAN

4251757300950