

Content

Portrait

ROHRflex
Conduits

FLEXAquick
Connectors


Metal
Conduits

Metal
Conduits
liquid tight

Plastic
Conduits

Special
Conduits

Connectors



**Metall-Sicherheitsverschraubung
gerade, Außengewinde**
inkl. Innentülle, Dichtring und O-Ring

**Metal connector, safety-type
straight, outer thread**
incl. ferrule, sealing and O-ring

AD OD	FLEXA No.				FLEXA No.				FLEXAquick								
	SPR-AS SPR-MS-NI SPR-VA				SPR-PA SPR-PU-AS SPR-PVC-AS												
Ø	PG DIN 40430	[IP 40]	mm	Ø l mm	[IP 65]	mm	Ø l mm	Ø B mm	C mm	D mm	SW1 mm	SW2 mm	kg/100	St. Pcs.			
10	7	5010.127.007	8 x 10	6,5	5010.128.007	7 x 10	6,0	19	7	28	15	17	1,5	50			
14	9	5010.127.009	11 x 14	10,0	5010.128.009	10 x 14	8,5	23	7	30	19	21	2,3	50			
17	11	5010.127.011	14 x 17	12,5	5010.128.011	13 x 17	11,5	27	7	30	23	25	3,0	50			
19	13,5	5010.127.013	16 x 19	14,5	5010.128.013	15 x 19	13,5	29	7	30	25	27	3,5	50			
21	16	5010.127.016	18 x 21	16,0	5010.128.016	17 x 21	15,5	31	7	30	27	29	4,0	50			
27	21	5010.127.021	23 x 27	21,5	5010.128.021	22 x 27	20,5	39	10	40	34	36	7,6	25			
36	29	5010.127.029	31 x 36	29,0	5010.128.029	29 x 36	27,5	48	10	40	43	45	10,1	25			
45	36	5010.127.036	40 x 45	38,0	5010.128.036	38 x 45	36,5	57	10	40	52	54	13,0	10			
56	48	5010.127.048	51 x 56	49,0	5010.128.048	49 x 56	47,5	70	10	45	63	66	20,0	1			
Kleine Verpackungseinheiten Small packing units																	
10	7	5010.427.007	8 x 10	6,5	5010.428.007	7 x 10	6,0	19	7	28	15	17	1,5	10			
14	9	5010.427.009	11 x 14	10,0	5010.428.009	10 x 14	8,5	23	7	30	19	21	2,3	10			
17	11	5010.427.011	14 x 17	12,5	5010.428.011	13 x 17	11,5	27	7	30	23	25	3,0	10			
19	13,5	5010.427.013	16 x 19	14,5	5010.428.013	15 x 19	13,5	29	7	30	25	27	3,5	10			
21	16	5010.427.016	18 x 21	16,0	5010.428.016	17 x 21	15,5	31	7	30	27	29	4,0	10			
27	21	5010.427.021	23 x 27	21,5	5010.428.021	22 x 27	20,5	39	10	40	34	36	7,6	10			
36	29	5010.427.029	31 x 36	29,0	5010.428.029	29 x 36	27,5	48	10	40	43	45	10,1	2			
45	36	5010.427.036	40 x 45	38,0	5010.428.036	38 x 45	36,5	57	10	40	52	54	13,0	2			
56	48	5010.427.048	51 x 56	49,0	5010.428.048	49 x 56	47,5	70	10	45	63	66	20,0	2			
FLEXAgraff®-AS																	
FLEXAgraff®-PU-AS																	
[IP 40]																	
[IP 65]																	
10	7	5010.127.007	8 x 10	6,5	5010.128.007	7 x 10	6,0	19	7	28	15	17	1,5	50			
14	9	5010.139.009	12 x 14	10,5	5010.127.009	11 x 14	10,0	23	7	30	19	21	2,3	50			
17	11	5010.127.011	14 x 17	12,5	5010.128.011	13 x 17	11,5	27	7	30	23	25	3,0	50			
19	13,5	5010.127.013	16 x 19	14,5	5010.128.013	15 x 19	13,5	29	7	30	25	27	3,5	50			
21	16	5010.127.016	18 x 21	16,5	5010.128.016	17 x 21	15,5	31	7	30	27	29	4,0	50			
27	21	5010.139.021	24 x 27	22,5	5010.140.021	23 x 27	20,5	39	10	40	34	36	7,6	25			
36	29	5010.127.029	31 x 36	29,5	5010.128.029	29 x 36	27,5	48	10	40	43	45	10,1	25			
45	36	5010.127.036	40 x 45	38,0	5010.128.036	38 x 45	36,5	57	10	40	52	54	13,0	20			
56	48	5010.127.048	51 x 56	49,0	5010.128.048	49 x 56	47,5	70	10	45	63	66	20,0	10			