


Male & Female Heat-Shrinkable Insulated Terminal - Connectors Pairs Boxed Set



(Matching colour Box)

Best. Nr.	Part/No.	Wire range	TAB Size (mm)	T (mm)	W (mm)	L1 (mm)	L (mm)	QTY (Pairs)	Colour
1661671	517-2-2020-04	0.5~1.5mm ² 22~16 AWG	2.80 x 0.80mm	0.8	2.8	6.5	32.5	30	Red
1661672	517-2-2021-04		4.80 x 0.80mm	0.8	4.8	6.7	32.7		
1661673	517-2-2022-04		6.40 x 0.80mm	0.8	6.4	7.7	33.7		
1661674	517-2-2023-05	1.5~2.5mm ² 16~14 AWG	2.80 x 0.80mm	0.8	2.8	6.5	32.5	30	Blue
1661675	517-2-2024-05		4.80 x 0.80mm	0.8	4.8	6.7	32.7		
1661676	517-2-2025-06		6.40 x 0.80mm	0.8	6.4	7.7	33.7		
1661677	517-2-2026-08	4.0~6.0mm ² 12~10 AWG	4.80 x 0.80mm	0.8	4.8	6.7	34.7	30	Yellow
1661678	517-2-2027-08		6.40 x 0.80mm	0.8	6.4	7.7	35.7		

Operating Temperature : 150°C max.

Material

Terminal : Brass

Insulation : HDPE

Plating : TIN

Tolerance : ±0.2

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2017 by Conrad Electronic SE.