

**SPECIFICATION:**

Insulator material	ABS
Contact material	Copper alloy
Rated current	1 A
Insulation resistance	DC 500V 100M Ω min
Contact resistance	30m Ω max
Dielectric withstand voltage	1000 VAC/minute
Operating temperature	-20 °C to +85 °C
Durability	750 mating cycle min
Plating	Gold

Art. Nr.**RND 765-00014**