



**M8 male 0° snap-in with cable**

PVC 3x0.25 gy UL/CSA 1.5m

M8  
Male straight  
3-pole  
Snap In

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**



Product may differ from Image

### Approvals



\* only for products with UL/CSA approved cable

### Form

08161

### Technical Data

|                               |                 |
|-------------------------------|-----------------|
| Operating voltage             | max. 60 V AC/DC |
| Operating current per contact | max. 4 A        |
| Locking of ports              | Snap In         |
| Protection                    | IP65            |

### Cables

|                             |                          |
|-----------------------------|--------------------------|
| Cable number                | 210                      |
| No./diameter of wires       | 3 × 0.25 mm <sup>2</sup> |
| Wire isolation              | PVC (br, bl, bk)         |
| Jacket Color                | gray                     |
| Shore hardness outer jacket | 85 ± 5A                  |
| Material (jacket)           | PVC (UL/CSA)             |
| Outer diameter              | approx. 4.5 mm           |
| Bend radius (fixed)         | 5 × outer Ø              |
| Bend radius (moving)        | 10 × outer Ø             |
| Temperature range (fixed)   | -30...+80 °C             |
| Temperature range (mobile)  | -5...+80 °C              |

### Commercial data

|                        |          |
|------------------------|----------|
| country of origin      | DE       |
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |