

SVS VALVE PLUG FORM A 18MM FIELD-WIREABLE


24...230V LED M16x1.5



Form A (18 mm) for pressure switch
24...230 V AC/DC
LED yellow (3)
metric

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



stay connected

Height: 41 mm

Product may differ from Image

Approvals



Form

29361

Technical Data

Operating voltage	24...230 V AC/DC
Operating current per contact	max. 4 A
Sealing range (cable diameter)	5...10 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16 × 1.5 mm
Protection	IP65 inserted and tightened (EN 60529), with gland

General data

Temperature range	-20...+60 °C
-------------------	--------------

Commercial data

country of origin	CZ
customs tariff number	85366990
minimum order quantity	1