



SIMATIC ET 200SP, BASEUNIT BU20-P12+A0+4B, BU-TYPE B1, PUSH-IN KLEMMEN, W/O AUX-TERMINALS, BRIDGED TO LEFT BU WXH: 20MMX117MM

Product type designation	
Supply voltage	
Rated value (DC)	24 V
Rated value (AC)	230 V; 110 V
Current carrying capacity	
up to 60 °C, max.	10 A
Galvanic isolation	
between backplane bus and supply voltage	Yes
Between process terminals and supply voltage	Yes
Between power bus and supply voltage	Yes
Isolation	
Isolation checked with	3250 V DC
Dimensions	
Width	20 mm
Height	117 mm
Weights	
Weight, approx.	48 g
<b>last modified:</b>	12.03.2015