

## Female contact crimp Pack d0,6 AWG28-24



Part number	21 01 100 9023
Specification	Female contact crimp Pack d0,6 AWG28-24
HARTING eCatalogue	<a href="https://b2b.harting.com/21011009023">https://b2b.harting.com/21011009023</a>

### Identification

Category	Contacts
Series	har-speed
Type of contact	Crimp contact
Description of the contact	Turned

### Version

Gender	Female
Performance level	1

### Technical characteristics

Conductor cross-section	0.08 ... 0.22 mm <sup>2</sup>
Conductor cross-section	AWG 24 ... AWG 28

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

### Commercial data

Packaging size	100
Net weight	0.1 g



Pushing Performance

## Commercial data

Country of origin	Romania
European customs tariff number	85366990