

## electronic pocket vernier calipers

Digital ABS point/fine callipers

Mitutoyo

### Application:

For measuring, e.g. small grooves and grooves

### Execution:

- Digimatic
- ABSOLUTE system for reliable measurement
- High-contrast display

### Advantage:

- High resistance to water and dust (IP67 degree of protection)
- Extra finely ground measuring arms

### Delivery:

Delivered in box



<b>Art. no.</b>	<b>32018 081</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	573-622-20
<b>Min./max. length measuring range</b>	0-150 mm
<b>Data transmission type</b>	DIGIMATIC
<b>Depth gauge rod</b>	Flat
<b>IP protection class</b>	IP 67
<b>With drive wheel</b>	No
<b>Error limit</b>	0.02 mm
<b>Length of jaw</b>	40 mm
<b>Design</b>	Metric
<b>Digit height</b>	9 mm
<b>Length of cross tips</b>	16.5 mm
<b>Digit increment</b>	0.01 mm
<b>Type of locating</b>	With locking screw
<b>Preset function</b>	No
<b>With mm / inch switching</b>	No
<b>Length</b>	233 mm
<b>With automatic shut off</b>	Yes
<b>Battery designation</b>	1,5 V SR44
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Weight of rechargeable battery/battery</b>	0.002 kg
<b>Battery voltage</b>	1.55 V
<b>Type of rechargeable battery/battery</b>	Silver oxide
<b>Calibration Group</b>	A
<b>ISO</b>	13385-1
<b>Functions</b>	Absolute function, Origin (Dimension preset), Automatic switch-off
<b>Gross Weight</b>	0.424 kg
<b>Product Group</b>	3MA

### EAN

4946368726816