



# MASTER TL5 High Efficiency

## MASTER TL5 HE 14W/835 1SL

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

### Product data

#### • General Characteristics

System Description	High Efficiency
Cap-Base	G5
Cap-Base Information	Green Plate
Bulb	T5 [16 mm]
Life to 10% fail	19000 hr
Preheat EL,3h	
Life to 50% fail	24000 hr
Preheat EL,3h	
LSF HF Preheat	99 %
2000h Rated,3h	
LSF HF Preheat	99 %
4000h Rated,3h	
LSF HF Preheat	99 %
6000h Rated,3h	
LSF HF Preheat	99 %
8000h Rated,3h	
LSF HF Preheat	99 %
12000h Rated,3h	
LSF HF Preheat	97 %
16000h Rated,3h	
LSF HF Preheat	84 %
20000h Rated,3h	

#### • Light Technical Characteristics

Color Code	835 [CCT of 3500K]
Color Rendering	85 Ra8
Index	
Color Designation	White
(text)	
Color Temperature	3500 K
Luminous Flux EL	1200 Lm
25°C, Rated	
Luminous Flux EL	1200 Lm
25°C, Nominal	

Luminous Flux Lamp	1350 Lm
EL 35°C	
Lum Efficacy Rated	86 Lm/W
HF 25°C	
Lum Efficacy Rated	99 Lm/W
HF 35°C	
LLMF HF 2000h	96 %
Rated	
LLMF HF 4000h	95 %
Rated	
LLMF HF 6000h	94 %
Rated	
LLMF HF 8000h	93 %
Rated	
LLMF HF 12000h	92 %
Rated	
LLMF HF 16000h	91 %
Rated	
LLMF HF 20000h	90 %
Rated	
Design Temperature	35 C
Chromaticity Coord- inate X	409 -
Chromaticity Coord- inate Y	394 -

#### • Electrical Characteristics

Lamp Wattage	14 W
Lamp Wattage EL	14.0 W
25°C, Rated	
Lamp Wattage EL	14 W
25°C, Nominal	
Lamp Wattage EL	13.7 W
35°C	
Lamp Voltage EL	86 V
25°C	



# MASTER TL5 High Efficiency

Lamp Voltage EL 35°C	82 V
Lamp Current EL 25°C	0.165 A
Lamp Current EL 35°C	0.170 A
Dimmable	Yes

## • Environmental Characteristics

Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content	1.4 mg
Energy consumption kWh/1000h	15 kWh

## • Measuring Conditions

Calibration Current	0.170 A
HF Generator Rated Voltage	167 V
Resistor	500 ohm


## • Product Dimensions

Base Face to Base Face A	549.0 (max) mm
Insertion Length B	553.7 (min), 556.1 (max) mm
Overall Length C	563.2 (max) mm
Diameter D	17 (max) mm

## • Product Data


Order code	927926083555
Full product code	927926083555
Full product name	MASTER TL5 HE 14W/835 1SL
Order product name	MASTER TL5 HE 14W/835 1SL/40
Pieces per pack	1
Packing configuration	40
Packs per outerbox	40
Bar code on pack - EAN1	8711500707659
Bar code on outerbox - EAN3	8711500867476
Logistic code(s) - 12NC	927926083555
ILCOS code	FDH-14/35/1B-L/P-G5-16/550
Net weight per piece	53.000 gr

## Dimensional drawing





## MASTER TL5 HE 14W/835 1SL

Product	A (Max)	B (Min)	B (Max)	C (Max)	D (Max)
TL5 14W/835/GP HE	549.0	553.7	556.1	563.2	17



G5

## Photometric data





© 2014 Koninklijke Philips N.V. (Royal Philips)  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2014, April 10  
data subject to change