


E11840



Wirable plug

SSTGH040MSSFKSK



Electrical data

Operating voltage [V] < 250 AC/DC

Operating conditions

Ambient temperature [°C] -25...60

Protection IP 67

Mechanical data

Weight [g] 12

Dimensions [mm] 16 x 16 x 54

Materials PA 6.6

Material nut PA 6.6

Remarks

Pack quantity 1 pcs.

Electrical connection

insulation displacement technology: 0.14...0.34 mm²; Cable sheath: Ø 3.5...6 mm

Electrical connection - plug

Connector: 1 x M12, straight; Moulded body: PA 6.6; Locking: PA 6.6



E11840

Wirable plug

SSTGH040MSSFKSK



Connection

