



MATERIAL LIST:

⑤	Conductor	Stranded&solid Cable	1	
④	Colour:	Transparent	1	
③	Gold plating:	50u"	8	
②	Contact blade:	COPPER ALLOY	1	
①	Housing	POLYCARBONATE UL 94-V2 used for the cable with the insulation OD from 0.94-1.1mm	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
-----	------------	------------------------	-------	--------

		NEW	2023-02-01	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

NOTES:

ELECTRICAL:

- Contact Resistance : 20MΩ MAX
- Insulation Resistance : 500MΩ MIN @ 100V DC min
- Withstand Voltage : 1000V AC
- Voltage, Current: 125V AC 1.5A @25°C

MECHANICAL:

- insertion force&withdrawal force:30N MAX.
- RJ45 Contact Life: 750 Times Min

ENVIRONMENTAL:

- Storage : -40° to+70°
  - Operation : -10° to+60°
- RoHS 2.0 and REACH Compliant

21.17.3095	VALUE STP Component Plug Cat.6A/Class EA, short body, 10 pcs.
ITEM NO.	DESC.

**SECOMP**