



HYPS-01712

12 Pole plug & socket pillar block polyamide 6a 250v



Female Part



Male Part

SPECIFICATION

| | |
|-----------------------------------|-------------------|
| Number of Poles | 12 |
| Body Material | Natural polyamide |
| Colour | Natural |
| Base Type | Raised |
| Max Conductor Size (Sq mm) | 2.5 |
| Max Current (A) | 6 |
| Max Voltage (V) | 250 |
| Max Temp Rating °C | 105 |
| Pitch (mm) | 10 |
| Height (mm) | 15.10 |
| Width (mm) | 18.6 |
| Length (mm) | 116.15 |

DISTRIBUTORS

