

DRAC GF 15**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**General ordering data**

Local product	Only available in certain countries
Type	DRAC GF 15
Order No.	7940084721
US order No.	6720005422
Version	DIN rail socket

DRAC GF 15

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

General ordering data

Local product Only available in certain countries

Local features

Availability United States

DIN-Rail Receptacles

Current Interrupting	Full rated current	Dielectric voltage	Withstands 1500V per UL498
Flame resistance, housing cover	Polyamide, 6/6 30% GF, UL94 nominal value V0 at 0.63 mm	Flame resistance, housing floor	PBT / Polycarbonate mixture, UL94 nominal value V0 at 0.63 mm
Frequency range, max.	60 Hz	Frequency range, min.	50 Hz
Max. torque for main contact	7 Nm	Spring	Stainless Steel
Wire connection cross section AWG, max.	AWG 10	Wire connection cross section AWG, min.	AWG 20

Rated data

Rated current 15 A Rated voltage 125 V