

## SNP2410C2



Article Number: 190-00121

Snapper Hose Clamps, .991"/1.115" Min/Max Diameter, POM, White, 100/pkg



Download drawing



Download spec sheet

### Base Data

Local Order Number SNP2410C2

Type SNP24

Color White (WH)

**Features and Benefits**

- Designed for quick, ratcheted installation and can be released and reused.
- Polyacetal material resists chemicals, corrosion and UV rays making it suitable for extreme environments.

**Product Description** HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.

**Short Description** Snapper Hose Clamps, .991"/1.115" Min/Max Diameter, POM, White, 100/pkg

### Product Dimensions

Fixation Method Plug-in mounting

Variant Closed

Width W2 (Imperial) 0.29 "

Width W2 (Metric) 7.37 mm

Diameter Min. (Imperial) 0.991 "

Diameter Min. (Metric) 25.17 mm

Diameter Max. (Imperial) 1.115 "

Diameter Max. (Metric) 28.32 mm

Wall Thickness WT (Imperial) 0.069 "

Wall Thickness WT (Metric) 1.8 mm

### Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 2000

### Material and Specifications

Material Polyacetal (POM)

Material Shortcut POM

Flammability UL94 HB

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes

