



KRAMER

C-HM/HM

High-Speed HDMI Cable

| HDMI | 4K/60 UHD (4:2:0) | 4K/60 UHD (4:4:4)
| 4K HDR



Kramer's C-HM/HM cable is your default choice for high-performance, HDMI cable. It supports signals up to 4K@60Hz (4:4:4), Deep Color, x.v.Color™, Lip Sync, 7.1 PCM, Dolby TrueHD, DTS-HD, CEC

FEATURES

Quality Performance - Kramer's HDMI cables provide an uncompressed digital link between consumer electronics equipment such as DVD players, set-top boxes and audio/video monitors such as plasma display screens for high-definition TVs

Max. Resolution - 4K@60Hz (4:4:4)

High-Quality Connectors - 24K gold-plated connectors resist corrosion, and offer the best possible connectivity

K-Lock Pull-Resistant Connectors - Provides 15lbs of restraining force for a non-slip connection

Varied Selection of Lengths - Available in versions of 0.9 to 15.2m (3, 6, 10, 15, 25, 35 and 50ft)



KRAMER

TECHNICAL SPECIFICATIONS

Type	High Speed and Standard Speed HDMI cables The 1-35 foot HDMI cables support the following resolutions: 480i, 480p, 720p, 1080i, 1080p
Conductor AWG	28 AWG (7/0.127)
Shield	Dual shield against EMI/RFI interference (a) Al- Mylar (b) Tinned Copper
Cable OD (mm)	7.3
Molded Connectors	Yes
Gold plated connectors:	Yes
Standards Compliance	HDR, HDCP
Flame test:	CL2



KRAMER

CONFIGURATIONS

C-HM/HM-3	High-Speed HDMI Cable
C-HM/HM-6	High-Speed HDMI Cable
C-HM/HM-10	High-Speed HDMI Cable
C-HM/HM-15	High-Speed HDMI Cable
C-HM/HM-25	High-Speed HDMI Cable
C-HM/HM-35	High-Speed HDMI Cable
C-HM/HM-50	High-Speed HDMI Cable