


	CPC
PRODUCT NO.	CS32770



- (1). Cable Spec: 28AWG (7/0. 127TC) *1PR+24AWG (7/0. 2TC) *2C+AL+D (1/0. 254BC) +B (64/0. 12LMS)
Jacket Material: PVC OD: 4.8mm
Colour: Black
Cable Printing: AWM STYLE 2725 80°C 30V VW-1 USB 2.0 High Speed Cable-RoHS
- (2). Connector A: USB2.0 B Female Solder Type
Insulation: White
Contact: Gold Plated
Shell: Fe, Nickel Plated
- (3). Connector B: USB B Male Solder Type
Insulation: White
Contact: Gold Plated
Shell: Fe, Nickel Plated
- (4). MOLDED: LD-PE
- (5). MOLDED: 45P PVC-BLACK
- (6). THUMB SCREW: NUT-NICKEL PLATED (#4-40)
- (7). CROSS SCREW: Nickel Plated (#4-40*15)
- (8). ELECTRONIC TEST:
A. OPEN/SHORT/INTERMITTENCE: 100%.
B. HI-POT: AC 300V 0.01S
C. INSULATION RESISTANCE: DC300V 0.01S 10MΩ (MIN)
D. CONDUCTIVE RESISTANCE: 5 OHM (MAX)

PIN OUT: (8)

SIDE:A	SIDE:B
USB2.0 BF	USB2.0 BM
1	1 RED
2	2 WHITE
3	3 GREEN
4	4 BLACK
SHELL	SHELL

GENERAL TOLERANCES (UNLESS SPECIFIED)							
LENGTH: X. ±1 .X ±0.2 .XX ±0.10		UNIT: mm	REV: 00			NAME	USB2.0 BM-BF
00	NEW	2019/03/29	2019/03/29	S. P. NO.		DWG. NO.	
REV	DESCRIPTION	DATE		P. O. NO.		PAGE	1/1
				SIZE			