

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0731375003](#)
Status: **Active**
Overview: [BNC Miniature RF Connectors and Cable Assemblies](#)
Description: BNC 50 Ohm, Right-Angle PCB Bulkhead Jack Receptacle, Panel Isolated, Black PBT Housing, Housing Height 13.20mm, Nut and Lockwasher included

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification SD-73137-5003-PKG \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E107635

General

Product Family RF/Coax Connectors
 Series [73137](#)
 Overview [BNC Miniature RF Connectors and Cable Assemblies](#)
 Product Name BNC
 Style PCB
 Type Miniature
 UPC 800753750258
 Wire/Cable Type N/A

Physical

Cable Attachment N/A
 Flammability 94V-0
 Gender Jack
 Keying to Mating Part None
 Net Weight 15.347/g
 Orientation Right Angle
 PCB Mounting Through Hole
 PCB Thickness - Recommended 3.20mm
 Packaging Type Tray
 Panel Mount Yes
 Panel Mount Method Bulkhead

Electrical

Frequency 2 GHz
 Impedance 50Ω
 Power / Voltage VOLT: 0500 Vrms@Sea Level


Solder Process Data

Duration at Max. Process Temperature (seconds) 010
 Lead-freeProcess Capability WAVE
 Max. Cycles at Max. Process Temperature 001
 Process Temperature max. C 245

Material Info

Reference - Drawing Numbers

Packaging Specification SD-73137-5003-PKG
 Sales Drawing SD-73137-5003-001



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/88/2018 (15 January 2019)
 Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[73137 Series](#)