

30°, 45°, 60° chamfer cutters for milling inserts TCMT 1102.., TCMT 16T3..


ATORN®

Application

Universal use for chamfering and deburring.

Version

- with straight shank in accordance with DIN 1835 B
- Shaft tolerance h6
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm, M4 = 5.2 Nm



Art. No.	16107316
Chamfer angle	45 Degree
Max. cutting edge diameter	16 mm
Min. cutting edge diameter	1.2 mm
Clearance length	20 mm
Length	70 mm
Shaft diameter	12 mm
Number of cutting edges	1 PCS
Suitable indexable insert no.	1
Suitable for indexable inserts	TC.. 1102..

EAN-Code

4050293111675