

Dial gauge micrometer

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- For direct GO/NG assessment of serial parts using an analogue or digital dial gauge
- 3-mm anvil stroke
- Brushed chromium-plated scale drum and sleeve
- Measuring faces carbide-tipped and micro-lapped

Advantage:

- A moving anvil enables quick measurements

Delivery:

Includes box, setting gauge (from 25 mm), adjustment wrench, excludes dial gauge



Art. no.	32016 199
Brand	MITUTOYO
Manufacturer Part Number	107-202
Min./max. length measuring range	25-50 mm
Digit increment, micrometer	0.01 mm
Repeat accuracy	2 µm
Measuring spindle increments	0.5 mm
Spindle clamping	Yes
Measurement force	10 N
Measuring surface diameter	6.35 mm
Calibration Group	AN
Gross Weight	0.725 kg
Product Group	3MA

EAN

4946368440590