

## Pneumatic ratchet screwdriver CP7829

tightening torque 95 Nm



### Application:

for heavy-duty screw-driving work in poorly accessible spots.

### Delivery:

in cardboard box



<b>Art. no.</b>	<b>75050 170</b>
<b>Brand</b>	CP
<b>Manufacturer Part Number</b>	8941078293
<b>Model</b>	CP7829
<b>Max. tightening torque</b>	95 Nm
<b>Max. idle speed</b>	225 rpm
<b>Air consumption</b>	312 l/min
<b>Tool holding device</b>	3/8-inch external square
<b>Connection thread</b>	G 1/4 inch
<b>Inner hose diameter</b>	10 mm
<b>Sound-pressure level</b>	96 dB
<b>Length</b>	272 mm
<b>Weight</b>	1.235 kg
<b>Gross Weight</b>	1.498 kg
<b>Product Group</b>	752

### EAN

0015451761660