


## 64576 1000 W 230 V

Halogen lamps, medium/high voltage, single-ended


### Areas of application

- Professional film and TV work



### Product family features

- Operation at mains voltage: 120 V | 230 V | 240 V
- Color temperature: 2,900 K | 3,000 K (with longer lifespan)
- Color temperature: 3,200 K (for professional film and TV work)
- Color temperature: 3,400 K (for maximum luminous efficacy)



# Product datasheet

## Technical data

### Product information

Order reference	64576
-----------------	-------


### Electrical data

Nominal wattage	1000.00 W
Nominal voltage	230 V

### Photometrical data

Color temperature	3200 K
-------------------	--------

### Dimensions & weight



Diameter	24.0 mm
Length	67.5 mm
Illuminated field	14.0*14.0 mm <sup>2</sup>
Filament diameter	14.0 mm

### Lifespan

Lifespan	75 h
----------	------

### Additional product data

Base (standard designation)	GX6.35
-----------------------------	--------

### Capabilities

Burning position	s
------------------	---

### Country specific categorizations

ANSI code	Other
-----------	-------

## Product datasheet

Order reference	64576
-----------------	-------

## Product datasheet

---

### References / Links

For further information on pinch technology, please refer to the following brochure:

“A whole lotta shakin’ goin’ on!” New halogen lamps with quartz pinch technology. (122 W 100 DE 08/05)

---

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.