

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



## Technical Datasheet

# tasker® C8015 – 8x0,15 mm<sup>2</sup> Braided Shielded Tinned Cable



**CATEGORY** Shielded Cable for Electronics and Data (See Data Network Catalogue)

- A:** Grey Soft PVC Sheath. - Outer Diam. Ø 6,50 (±0,20) mm
- B:** Braided Shielding O.F.C. Tinned Copper covering 85%
- C:** Cores Insulation with Soft PVC– DIN 47100 Standards.  
Diam. Ø 1,20 mm (±0,20) mm. Stranded with waste filler between conductors and wrapped with Mylar Tape.
- D:** Stranded O.F.C. Tinned Copper formation 19x0,10 mm.  
Nom. Cross section 8x0,15 mm<sup>2</sup>

**MARKING** tasker® C8015 8x0,15 - 25 AWG Professional Data Transmission Shielded cable  
 Made in Italy

**CUSTOM** This product is also available in L.S.Z.H., PE, PUR, with or without Steel Armor.

### Cable Properties

<b>Conductor Resistance</b>	120 Ω/Km ± 5%
<b>Capacity Core/Core</b>	100 pF/mt
<b>Capacity Core/Shield</b>	180 pF/mt
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-15/+70°C

<b>USE</b>	<b>X</b>	Indoor	Interno Edificio	<b>INSTALLATION</b>	<b>X</b>	Fixed	Fissa	<b>INFORMATION</b>	<b>X</b>	RoHS2 Compliant
<b>Impiego</b>		Outdoor Limited	Esterno Limitato	<b>Posa</b>	<b>X</b>	Flexible Limited	Flessibilità limitata	<b>Informazioni</b>	<b>X</b>	Ver. A / 18.07.16
		Outdoor Direct Burial	Esterno Interrato			Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			