

9 VOLT BATTERY STRAPS

Designers' Choice



PREMIUM 9 VOLT BATTERY STRAPS

Rigidly constructed. Nickel plate, male and female contacts. Female contacts are spring temper. Accepts numerous insertions to meet U.L. approved standards. Provides excellent mechanical strength and low contact resistance. Wire leads (red and black) are soldered for increased reliability. Wires have tinned copper conductors, PVC insulation and the ends are stripped for easy connection.

Wires are rated to 176°F (80° C) and 300V and meet UL/CSA #1061/#1007 requirements.

Modifications available with different lead lengths.

*Tolerance on lead length +/- .250




Cover Sizes: 1.125 x .530
Contacts: Phos. Br., Nickel Plate
Wire: #26 AWG, 7/34
End Strip: .250 Long, Tinned

VINYL COVER

- FULLY INSULATED
- RIGID ASSEMBLY

I - STYLE

CAT. NO.	*LEAD LENGTH
2238	4.00
2239	6.00
2240	8.00



Cover Sizes: 1.000 x .687
Contacts: Phos. Br., Nickel Plate
Wire: #26 AWG, 7/34
End Strip: .250 Long, Tinned

T - STYLE with Strain Relief

CAT. NO.	*LEAD LENGTH
2241	4.00
2242	6.00
2243	8.00



FIBRE BASE

- .062 THICK

Cover Sizes: 1.030 x .535
Contacts: Steel, Nickel Plate
Wire: #22 AWG, 7/30 Prebond
End Strip: .375 Long, Tinned

CAT. NO.	*LEAD LENGTH
68	None
72-4	4.00
72	7.00
72-8	8.00




Cover Sizes: .900 x .575
Contacts: Steel, Nickel Plate
Wire: #22 AWG, 7/30 Prebond
End Strip: .375 Long, Tinned

FIBRE COVER

- FULLY INSULATED
- FLEXIBLE ASSEMBLY

I - STYLE

CAT. NO.	*LEAD LENGTH
83-4	4.00
83	6.50
83-8	8.00



Cover Sizes: .900 x .575
Contacts: Steel, Nickel Plate
Wire: #22 AWG, 7/30 Prebond
End Strip: .375 Long, Tinned

T - STYLE

CAT. NO.	*LEAD LENGTH
85-4	4.00
85-6	6.50
85-8	8.00

ECONOMY 9 VOLT BATTERY STRAPS

When product cost is of the utmost importance these economy battery straps will suit your needs. Brass contacts, nickel plated with vinyl covering. Wires have tinned copper conductors, PVC insulation and the ends are stripped for easy connection. Wires meet UL/CSA #1007 requirements.

Modifications available with different lead lengths.

*Tolerance on lead length +/- .250




Cover Sizes: 1.125 x .530
Contacts: Brass, Nickel Plate
Wire: #26 AWG, 7/34
End Strip: .250 Long, Tinned

VINYL COVER

- FULLY INSULATED
- RIGID ASSEMBLY

I - STYLE

CAT. NO.	*LEAD LENGTH
232	4.00
233	6.00
234	8.00



Cover Sizes: 1.000 x .687
Contacts: Brass, Nickel Plate
Wire: #26 AWG, 7/34
End Strip: .250 Long, Tinned

T - STYLE with Strain Relief

CAT. NO.	*LEAD LENGTH
235	4.00
236	6.00
237	8.00


DUAL 9 VOLT BATTERY STRAPS

These dual battery straps are pre-wired for connecting two 9 Volt batteries. Available for either series or parallel connection. Base made from fibre material with steel, nickel plated contacts. Wires have tinned copper conductors, PVC insulation and the ends are stripped for easy connection. Wires meet UL/CSA #1061 requirements.



*Tolerance on lead length +/- .250


PARALLEL



Contacts: Steel, Nickel Plate
Wire: #22 AWG, 7/30 Prebond
End Strip: .375 Long, Tinned

CAT. NO.	*LEAD LENGTH
227	7.00

SERIES



Contacts: Steel, Nickel Plate
Wire: #22 AWG, 7/30 Prebond
End Strip: .375 Long, Tinned

CAT. NO.	*LEAD LENGTH
229	7.00