



Digital Signage is the remote-controlled distribution and playback of digital content (TV programs, advertising, menus, and every sort of information) on networks of displays. These displays can range from digital billboards to much smaller screens, either at a single location or across multiple sites. It's all about targeting the audience with relevant information. Digital signage enables users to display their messages more dynamically and targeted.

ALLNET has demonstrated a Digital Signage application on android platform. The application provides the features of updating the content from remote web browser, playback of video content, image, HTML web pages and scrolling text messages.


Key Features:

- Android 7.1 Operating System
- Rockchip RK3288 Quad-core CPU
- 2/4GB DDR3 + 8/16GB Flash
- 802.11 b/g/n internal Wifi
- 3G/WIFI/WLAN Network Connection
- Remote Management Software
- Portrait & Landscape Display Mode
- 1080P Display Output
- Auto-Dispenser
- Waterproof Casing
- PCAP Touch Screen (option)
- Battery (option)
- Camera Option (For Security, Body Temperature Etc)
- Free Standing Bracket
- Replaceable Drip Trays 5000ML Volume
- Indicator of Sanitizer Volum
- Software to Watch Sanitizer Volum Remotely
- Metal Body Housing
- Tempered Protection Glass

Designed for:

- POS
- Hotel
- Self-service Terminal
- Public Information Display
- Hospitality
- In-vehicles and Transportation

ALL-WD21SAN/A70-STAND



Specifications

PANEL	Panel Model	21.5inch TFT LED	HDMI DISPLAY	Output Mode	HDMI 480P
	Max Resolution	1920x1080		HDMI 576P	
	Aspect Ratio	16:09		HDMI 720P 50Hz	HDMI 720P 60Hz
	Pixel Pitch	0.24825x0.24825		HDMI 1080I 50Hz	HDMI 1080I 60Hz
	Viewing Angle	89/89/89/89		HDMI 1080P 24Hz	HDMI 1080P 50Hz
	Contrast Ratio	3000:1		HDMI 1080P 60Hz	
	Brightness	500cd/m ²			
	Response Time	18ms			
	Display Area (mm)	476.64x268.11mm			
	Panel Size(mm)	495.6x292.2x8.6mm			
	Screen Weight	1.67Kg			
	Lamp Type	WLED			
INTERNAL MEDIA PLAYER	CPU	Quad-core ARM Cortex-A17, 1.8GHz	ON-SCREEN DISPLAY LANGUAGES	English, French, German, Italian, Polish, Russian, Simplified Chinese, Spanish, Turkish, Arabic, Japanese, Traditional Chinese etc.	
	GPU	ARM Mali-T764	DISPLAY MODE	Portrait & Landscape	
	RAM	2/4GB DDR3	TOUCH	PCAP Touch (optional)	
	ROM	8/16 GB Flash	POWER	Mains Power Consumption	AC 100-240V, 50-60 Hz
	OS	Android 7.1			30W
CONNECTOR	USB 2.0	X2	DIMENSION & WEIGHT	Machine Size	799.4x171.2x384.5mm/450x350x1018(stand)
	HDMI (Output)	X1		Machine Weight	38kg
	SD	X1		Carton Size	940x320x620mm/1100x490x630(stand)
	Rj45	X1		Carton Weight	50KG
	3G SIM (Optional)	X1	OTHER	Regulatory Approvals	CE, FCC, ROHS
CONNECTIVITY	WiFi	Built-in WiFi 802.11B/G/N		Warranty	2 years warranty
FILE SUPPORT	Video	H.264, MKV, WMV9, MPEG 1/2/4, HD Divx, Xvid, RM/RMVB;	ACCESSORIES	Included	Power supply, Tools and Screws
	Image	BMP/PNG/GIF/JPEG			
	Audio	MP3,WMA,WAV,EAAC+, MP2 dec, Vorbis (Ogg), AC3, FLAC, APE, BSAC			
	Scrolling Text	txt			