


### Notes:

1. Cable: UL2725, USB 2.0, AL+B-foil, #28\*1P+#28\*2C, black colour, OD=4.0±0.2mm, PVC jacket
2. Length: xxM
3. Connectors: USB4P(A)type plug\*1(white insulator)(pin 3U")
4. Mold: molding USB Type
5. Contacts:

USB4P(A)	1	2	3	4	64
Micro USB5P	1	2	3	5	64
	RED	WHITE	GREEN	BLACK	DRAIN
		PAIR			



### 6. Test machine condition:

- A. 100% open, short & intermittance test
- B. Conductor resistance: 3Ω Max:
- C. Insulation resistance: 5M Min/,10ms:

