

VESA 100/75 Adapter for Pro Devices, IP20 additional information, amount and content: see technical data



General information	
Product type designation	Fixing element
Installation type/mounting	
Mounting	VESA 100 mm / 75 mm with M6 thread
Mounting type	Support arm with VESA 100 mm or 75 mm
Degree and class of protection	
IP (at the front)	IP20 (depending on mounting)
Ambient conditions	
Suited for indoor use	Yes
Suited for outdoor use	No
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	70 °C
Relative humidity	

- Operation, max. 90 %
- Condensation permissible No

Mechanics/material

- Material steel
- Aluminum No

Dimensions

- Width 135 mm
- Height 120 mm
- Depth 67.5 mm

Scope of supply

- Delivery quantity in pieces 1; VESA round tube adapter 100/75 suitable for PRO devices, max. IP20 attainable

Other

- Merchandise Yes; VESA 100/70 adapter
- Manufacturer name QUERUM smart engineering
- Manufacturer's address An der Autobahn L8, 91161 Hilpoltstein, Germany
- Note: Max. load 35 kg

last modified: 10/13/2017