

PRODUCT-DETAILS

3210

THERMOPLASTIC BUSHING



General Information

Extended Product Type	3210
Product ID	7TAD013590R0000
EAN	0786210032108
Catalog Description	THERMOPLASTIC BUSHING
Long Description	One Piece Non Metallic Knockout Bushing, Thermoplastic, Knockout Size 0.875 for Use with Rigid/IMC Conduit

Additional Information

Application	To Bush Knockout Openings In Metal Boxes or Enclosures
Product Type	Knockout Bushings & Plugs

Ordering

EAN	0786210032108
UPC	786210032108
Customs Tariff Number	3926909985

Technical

Number of Batteries	0
Color	Black
Material	Polycarbonate

Size 0.875 Inch

Environmental

WEEE Category Product Not in WEEE Scope

Container Information

Package Level 1 Units	100 piece
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	5 in 127 mm
Package Level 1 Width	4.5 in 114 mm
Package Level 2 Units	500 piece
Package Level 2 Height	5.5 in 140 mm
Package Level 2 Depth / Length	10.5 in 267 mm
Package Level 2 Width	9 in 229 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	3210
Instructions and Manuals	3210

Classifications

UNSPSC 39121312

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Rigid Cable Protection Systems

