

Myriad Deco IP65 White Bezel

MYRIAD DECO IP65 SPOT 3000K DALI SILVER WBEZ
2059242



Product features

- MYRD IP ST 3K DALI SIL WBEZ



PRODUCT OVERVIEW

| | |
|---------------------------------|---|
| Product name | MYRIAD DECO IP65 SPOT 3000K DALI SILVER WBEZ |
| Technology | LED |
| Housing | Aluminium |
| Mount | Ceiling recessed mounting |
| Environment | Interior |
| General application | Hospitality, Office, Residential & Consumer, Retail |
| ETIM Class | EC001744 |
| Warranty | 5 years |
| Fixture luminous flux (lm) | 1106 |
| Luminaire efficacy (lm/W) | 111 |
| LOR (%) | 100 |
| Colour temperature (K) | 3000 |
| Light colour | Warm White |
| CRI (Ra) | 90 |
| Colour Variation Initial (SDCM) | SDCM3 |
| Beam Angle (°) | 28 |
| Photobiological Risk Group | RG1 |
| Total power consumption (W) | 10 |
| Electrical protection | Class II |
| Control gear type | Electronic ballast |
| Dimming method | DALI |
| Minimum dimming level (%) | 1 |
| Housing colour | Silver |
| IP rating | IP65/20 |
| IK rating | IK02 |
| Product EAN number | 5025768592425 |

DATA TABLE

General data

| | |
|--------------|--|
| Product name | MYRIAD DECO IP65 SPOT 3000K DALI SILVER WBEZ |
| Technology | LED |

Myriad Deco IP65 White Bezel

MYRIAD DECO IP65 SPOT 3000K DALI SILVER WBEZ

2059242

| | |
|---|---|
| Housing | Aluminium |
| Mount | Ceiling recessed mounting |
| Environment | Interior |
| General application | Hospitality, Office, Residential & Consumer, Retail |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC001744 |
| Warranty | 5 years |

Optical data

| | |
|---------------------------------|------------|
| Fixture luminous flux (lm) | 1106 |
| Luminaire efficacy (lm/W) | 111 |
| LOR (%) | 100 |
| Colour temperature (K) | 3000 |
| Light colour | Warm White |
| CRI (Ra) | 90 |
| Colour Variation Initial (SDCM) | SDCM3 |
| Adjustable chromaticity | N |
| Beam Angle (°) | 28 |
| Photobiological Risk Group | RG1 |

Electrical data

| | |
|--|--------------------|
| Total power consumption (W) | 10 |
| Mains voltage (V) | 230-240V |
| Electrical protection | Class II |
| Control gear type | Electronic ballast |
| Transformer required | Yes |
| Dimming method | DALI |
| Minimum dimming level (%) | 1 |
| Drive current (mA) | 250 |
| Energy Efficiency Class (A->G) of contained light source | E |
| Nominal Frequency (Hz) | 50/60Hz |

Lifetime data

| | |
|------------------|--------|
| Lifespan L70 B50 | 100000 |
| Lifespan L80 B20 | 100000 |
| Lifespan L90 B10 | 68500 |

Physical data



| | |
|---|-----------------|
| Housing colour | Silver |
| IP rating | IP65/20 |
| IK rating | IK02 |
| Diffuser finish | Bezel (or Ring) |
| Nominal Product Height (mm) | 72 |
| Nominal Product Diameter (mm) | 90 |
| Cutout Dimensions (W x L in mm or Diameter in mm) | 76 |
| Weight (kg) | 0.44 |
| Recessed Depth (mm) | 72 |

Myriad Deco IP65 White Bezel MYRIAD DECO IP65 SPOT 3000K DALI SILVER WBEZ 2059242

Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5025768592425 |
| Packaging single length / height (cm) | 17.5 |
| Packaging single width (cm) | 15.0 |
| Packaging single depth (cm) | 17.5 |
| DUN14 (outer) | 05025768592425 |
| Units per outer package | 1 |
| Packaging outer length / height (cm) | 17.5 |
| Packaging outer width (cm) | 15.0 |
| Packaging outer depth (cm) | 17.5 |

PHOTOMETRY



TECHNICAL DRAWINGS

