

Hydraulic short stroke cylinder RCS



Execution:

- Single-acting cylinder.
- Without fastening thread on cylinder head and piston rod.
- Operating pressure of 700 bar
- With spring return mechanism and scraper ring.
- Scraper ring.
- Piston rod with nickel plating.
- Model RCS 1002 with carry handle.
- For RCS 101-502 models, the coupling sleeve is inserted at an angle of 5°.

Advantage:

- Retaining ring prevents piston rod from being pushed out.

Delivery:

1x ENERPAC hydraulic short stroke cylinder RCS 101.



Art. no.	29511 060
Brand	ENERPAC
Manufacturer Part Number	RCS502
Model	RCS 502
Max. compressive force	435 kN
Lift height	60 mm
Oil capacity	373 cm ³
Construction height, retracted	122 mm
Outer diameter	124 mm
Weight	10 kg
Gross Weight	10.020 kg
Product Group	258