

Electronic micrometer set

0-100 mm IP65



Application:

For measuring e. g. shaft diameters, external dimensions on workpieces etc.

Execution:

- Carbide measuring faces
- RESET (resetting the display)
- ABS (display can be set to zero without losing the reference to the ORIGIN)
- mm/inch
- ORIGIN (measurement pre-setting)
- LOCK function (keypad lock)
- TOL (input of tolerances and warning limits)
- DATA (in connection with data connection cable)
- HOLD (measured value storage)

Delivery:

Operating instructions, battery, setting gauge (from a measuring range of 25-50 mm), travel case



| | |
|---|--------------------------|
| Art. no. | 31403 410 |
| Brand | MAHR |
| Manufacturer Part Number | 4157015 |
| Min./max. length measuring range | 0-100 mm |
| Digit increment | 0.001 mm |
| Data transmission type | MarConnect bidirektional |
| Measuring surface diameter | 6.5 mm |
| Measuring spindle increments | 0.5 mm |
| IP protection class | IP 65 |
| Spindle clamping | No |
| Number of bracket measuring screws | 4 |
| Number of setting dimensions | 3 |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 3V CR2032 Lithium |
| Calibration Group | D, E |
| Gross Weight | 3.500 kg |
| Product Group | 305 |

EAN

4059192058517