

KFM 9-3 RF laminate trimmer

900 watt

metabo

Application:

Compact metal laminate trimmer for 45° chamfers and radii of 2 to 3 mm on visible edges

Version:

- One-touch controller: Patented, tool-free milling depth setting in 0.1-mm increments
- Slimline milling head with standard carbide indexable inserts and thrust ball bearings for working on pipes and on curved surfaces
- Guide stop for uniform work results and high surface quality when processing straight metal sheets
- Oxide-free and burr-free surfaces in ideal preparation for applying powder or paint coatings for maximum corrosion protection

Advantage:

- Snap points for short setup times, prevent unwanted adjustment of cutting depth when working

Delivery:

2 each of carbide indexable inserts 45° chamfer, radius R2, radius R3, guide stop, screwdriver, dust filter, additional VibraTech handle in MetaLoc case



Art. no.	70309 400
Max. idle speed	11500 rpm
Model	KFM 9-3 RF
Manufacturer Article Number	601751700
Power input	900 W
Power output	470 W
Max. chamfer height 45°	4 mm
Max. chamfer width 45°	6 mm
Weight	2.5 kg
Cable length	4 m
With soft start	Yes
With overload protection	Yes
With restart protection	Yes
With electronic feedback	No

EAN-Code

4007430293404