



Introducing RW-175-E

Highly flame-resistant, high-temperature, chemical-resistant RW-175-E tubing provides tough, semirigid, very-thin-wall insulation and strain relief of multipin connectors, solder joints and other delicate electrical connections and terminations. It is well-suited for applications that require dense packing of components or visual inspection of covered components. It is especially suitable for applications requiring outstanding abrasion and cut-through resistance and superior chemical and solvent resistance. Its high temperature performance meets or exceeds military and industrial standards.

KEY FEATURES

- 2:1 shrink ratio for all standard sizes
- Tough, semirigid, very-thin-wall insulation
- High flame-resistance, meeting the requirements of IEC 60684-2, also with UL and CSA VW-1 flammability rating
- High temperature performance that meets or exceeds military and industrial standards
- Protection from most industrial solvents, fuels, and chemicals
- Offers improved clarity (clear version) and increased resistance to crazing when compared to previously offered solutions

APPLICATIONS

- Appliances
- Military and commercial aircraft
- Commercial electronics and communication
- Industrial equipment

ELECTRICAL

- Provides excellent electrical insulation
- Not recommended for use as a primary insulator at temperatures exceeding 135°C [275°F]

MECHANICAL

- Tough modified polyvinylidene fluoride material provides outstanding abrasion and cut-through resistance
- Excellent for strain relief when installed on delicate electrical connections and terminations

TEMPERATURE RATING

- Full recovery temperature: 175°C [347°F]
- Operating Temperature range: -55°C to 175°C [-67°F to 347°F]

STANDARDS AND SPECIFICATIONS

- RW-3029/1
- UL 224 VW-1
- CSA C22.2 No. 198.1-98 VW-1

ORDERING INFORMATION


- Colour: Clear (-X) (standard); Black (-O) (nonstandard)
- Standard packaging (-STK): 1.2m [4 ft.] lengths
Optional packaging (-SP): Spool, varying lengths (consult TE for details)
- Ordering description: Specify product name, size, colour and packaging; for example, RW-175-E-3/16-X-STK.

SAMPLES NOW AVAILABLE

te.com/products/RW-175-E



RW-175-E DIMENSIONS



Size	Minimum Expanded I.D. (D)		Maximum Recovered I.D. (d)		Nominal Recovered Jacket Wall (W)	
	mm.	in.	mm.	in.	mm.	in.
3/64	1.20	.046	.60	.023	.25 ± .051	.010 ± .002
1/16	1.60	.063	.80	.031	.25 ± .051	.010 ± .002
3/32	2.40	.093	1.20	.046	.25 ± .051	.010 ± .002
1/8	3.20	.125	1.60	.062	.25 ± .051	.010 ± .002
3/16	4.80	.187	2.40	.093	.25 ± .051	.010 ± .002
1/4	6.40	.250	3.20	.125	.33 ± .051	.013 ± .002
3/8	9.50	.375	4.80	.187	.33 ± .051	.013 ± .002
1/2	12.70	.500	6.40	.250	.33 ± .051	.013 ± .002
3/4	19.10	.750	9.50	.375	.43 ± .076	.017 ± .003
1	25.40	1.000	12.70	.500	.48 ± .076	.019 ± .003
1-1/2	38.10	1.500	19.10	.750	.51 ± .076	.020 ± .003
2	50.00	2.000	25.40	1.000	.51 ± .076	.020 ± .003

RW-175 ORDERING DESCRIPTION


Example 1:

RW-175-E-3/8-X-STK



Example 2:

RW-175-E-3/4-O-SP



te.com/products/RW-175-E



PRODUCT OFFERING

Material Description	Material Number
RW-175-E-3/64-X-STK	CV20922001
RW-175-E-3/64-X-SP	CV20914001
RW-175-E-1/16-X-STK	CV25362001
RW-175-E-1/16-X-SP	CV21254001
RW-175-E-3/32-X-STK	CV25382001
RW-175-E-3/32-X-SP	CV21204001
RW-175-E-1/8-X-STK	CV25332001
RW-175-E-1/8-X-SP	CV21424001
RW-175-E-3/16-X-STK	CV25372001
RW-175-E-1/4-X-STK	CV25342001

Material Description	Material Number
RW-175-E-1/4-X-SP	CV21104001
RW-175-E-3/8-X-STK	CV25852001
RW-175-E-3/8-X-SP	CV21364001
RW-175-E-1/2-X-STK	CV25902001
RW-175-E-1/2-X-SP	CV25894001
RW-175-E-3/4-X-STK	CV37312001
RW-175-E-3/4-X-SP	CV37304001
RW-175-E-1-X-STK	CV37322001
RW-175-E-1-1/2-X-STK	CV51572001

SAMPLE INVENTORY

RW-175-E-3/64-X-STK
RW-175-E-1/16-X-STK
RW-175-E-3/32-X-STK
RW-175-E-1/8-X-STK
RW-175-E-3/16-X-STK
RW-175-E-1/4-X-STK
RW-175-E-3/8-X-STK
RW-175-E-1/2-X-STK
RW-175-E-3/4-X-STK
RW-175-E-1-X-STK
RW-175-E-1-1/2-X-STK

te.com/products/RW-175-E



PROPERTY REQUIREMENTS

Property	Unit	Requirement	Test Method
PHYSICAL			
Dimensions	mm	Table 1	RW-3029/1, Section 2.2
Longitudinal Change	Percent	+0, -10 maximum	IEC 60684-2
Tensile Strength	MPa	35 minimum	IEC 60684-2
Ultimate Elongation	Percent	150 minimum	IEC 60684-2
Secant Modulus (expanded)	MPa	690	IEC 60684-2
Specific Gravity		1.8 maximum	IEC 60684-2
Low Temperature Flexibility 4 hours at -55°C ± 2°C (-67 ± 4°F)		No cracking	IEC 60684-2
Heat Shock 4 hours at 300 ± 5°C (572 ± 9°F)		No dripping, flowing or cracking	IEC 60684-2
Heat Aging 168 hours at 200 ± 2°C (392 ± 4°F) Followed by test for: Ultimate elongation	Percent	75 minimum	IEC 60684-2
ELECTRICAL			
Breakdown Voltage Recovered wall thickness 0.25mm Recovered wall thickness 0.30mm Recovered wall thickness 0.45mm Recovered wall thickness 0.55mm	kV	5.0 minimum 6.0 minimum 9.0 minimum 10.0 minimum	IEC 60684-2
Volume Resistivity	Ohm-cm	1 X 10 ¹³ minimum	IEC 60684-2
CHEMICAL			
Corrosive Resistance 16 hours at 150°C		Noncorrosive	IEC 60684-2
Copper Contact		No corrosion of mirrors above 8%	IEC 60684-2
Flammability Average Time of Burning	Seconds	15 maximum	IEC 60684-2
Fungus Resistance Followed by tests for: Tensile Strength Ultimate Elongation	Mpa Percent	34.5 minimum 150 minimum	ISO 846, Method B IEC 60684-2 IEC 60684-2
Dielectric Strength Sizes 3/64 through 1/2 Sizes 3/4 through 2	Volts/mm	31,500 23,600	IEC 60684-2
Water Absorption 24 hours at 23 ± 2°C (73 ± 4°F)	Percent	0.5 maximum	IEC 60684-2
Fluid Resistance 24 hours at 23 ± 3°C Gasoline (ISO 1817 Liquid B) Phosphate Base (ISO 1817 Liquid 103) Isopropyl Alcohol Propanol 25% White spirit 75% Methyl Ethyl Ketone Inhibited Potassium Acetate in Water 50% Ethylene Glycol 80% Water 20% 24 hours at 70 ± 2°C Kerosene (ISO 1817 Liquid F) Silicone Base (S-1714) Synthetic Base (ISO 1817 Liquid 101) Mineral Base (ISO 1817 Oil No 2) Mineral Base (O-1176) 24 hours at 50 ± 2°C Mineral Base (O-142) Followed by tests for: Tensile Strength Elongation	MPa Percent	25 minimum 150 minimum	IEC 60684-2 RW-3029/1, Table 2

While TE has made every reasonable effort to ensure the accuracy of the information in this flyer, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this flyer are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

te.com/products/RW-175-E

