


MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it


Technical Datasheet
tasker® C114 – 2x0,25 mm² Even in White
Low Capacity Balanced Microphone Cable



A	B	C	D	E
---	---	---	---	---


CATEGORY **Balanced Microphone Cable** (See Audio Catalogue)

- A:** Soft **PVC** Sheath – Available in different color .
Outer cable Diam. Ø 6,00 (±0,20) mm.
- B:** Shielding O.F.C. red copper Spiral covering 100%.
- C:** The cores will be stranded in a pair with textile waste filler between
conductors and wrapped with not woven polyester based tape.
- D:** Core Insulation with a compact PE, colored one Orange and one
Transparent. Diam. Ø 1,50 (±0,20) mm.
- E:** O.F.C. red copper, formation 8x0,20 mm.
Nom. Cross section 2x0,25 mm².

MARKING **tasker® C 114 2x0.25 – 23 AWG O.F.C. Low Capacitance Flex Microphone Cable**
 Made in Italy

CUSTOM This product is also available in **L.S.Z.H., PE, PUR**, with or
 without **Steel Armor**.

Attenuation Test – Start 9 KHz – Stop 25 KHz



Cable Properties

Conductor Resistance	75 Ω/Km ± 5%
Capacity Core/Core	55 pF/mt
Capacity Core/Shield	90 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	INSTALLATION	<input checked="" type="checkbox"/>	Fixed	Fissa	INFORMATION	<input checked="" type="checkbox"/>	RoHS2 Compliant
Impiego	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	Posa	<input checked="" type="checkbox"/>	Flexible Limited	Flessibilità limitata	Informazioni	<input checked="" type="checkbox"/>	Ver. C/ 06.06.2016
		Outdoor Direct Burial	Esterno Interrato		<input checked="" type="checkbox"/>	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			