


30847-464 FRONT PANEL, UNSHIELDED, 4 U, 63 HP, 2.5 MM, AL, FRONT ANODIZED, REAR CONDUCTIVE



0

KEY FEATURES

Partial width front panel, Al, 2.5 mm

Al, front anodized, conductive

PRODUCT ATTRIBUTES

| Type: Front Panel without Handle |
|--|
| Accessory Type: Front panel |
| Mounting: Screw-on Front |
| EMC Shielding: No |
| Material: Aluminum |
| Front Finish: Anodized |
| Rear Finish: Conductive |
| Treated Edges: No |
| Rack Height: 4 U |
| Height: 172.9 mm |
| Width: 319.7 mm |
| Depth: 2.5 mm |
| Complies With: IEC 60297-3-101; IEEE 1101.1/10 |

ADDITIONAL PRODUCT DETAILS

Front panel, unshielded, front anodized and rear conductive.

Please order fixing material (sleeves, collar screws) separately.

CERTIFICATIONS



North America

All locations +1.763.422.2661 Chat with us: schroff.nvent.com

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

nVent.com

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

Our powerful portfolio of brands:

nVent reserves the right to change specifications without notice.