

Loudspeakers

Order code	Manufacturer code	Description
35-0130	n/a	66MM FERRITE 8 OHM SPEAKER (RC)
77-1280	n/a	n/a

Loudspeakers	Page 1 of 3
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

RAPID ELECTRONICS LTD		REF NO.931541-2
		DATE: 22-11-1993
MODEL/REF: RD-6608F/35-0130		
DESCRIPTIONS	SPECIFICATION	TEST CONDITION
VOICE COIL IMP.	8Ω +/- 15%	AT 800 Hz V
OPERATION	MUST BE NORMAL	PROGRAM SOURCE V
BUZZES & RATTLES	MUST BE NORMAL	SINE WAVE 1.55 V
RESONANT FREQ.	260 +/- 50 Hz	WITHOUT BAFFLE
OUTPUT SPL	AVG. 87 +/- 3 dB	AT 0.5M/1W 0.6 0.8 1.0 1.2K Hz
FREQ. RESPONSE	FO -- 4K Hz	
RATED FREQ. RESP.	Hz	
RATED POWER INPUT	0.3W	
MAX. POWER INPUT	0.5W	
LOAD TEST	AFTER TEST MEET SPEC.	WHITE NOISE 0.3W/5 HOURS
HEAT TEST	AFTER TEST MEET SPEC.	70+/-2° C 20/25R.H. 5 HOURS
HUMIDITY TEST	AFTER TEST MEET SPEC.	40+/-2° C 90/95R.H. 5 HOURS
DISTORTION	5% MAX.	RATED POWER INPUT 800 Hz
TOTAL FLUX	MAX WELL	
FLUX DENSITY	GAUSS	
MAGNET	DIA 32x18/6/0.57 OZ	
WEIGHT	56 GRAMS / OZ	
BAFFLE OPENING	%	
V.C. TEMPERATURE	80° C MAX.	

