

## 30m Reel 9 Way Grey UL2651 Ribbon Cable

### Notes:



Insulation material: PVC  
Colour: Grey

### Specification:

Rating: 300V  
Conductor size: 28awg or 30awg  
Insulation resistance: 100mΩ/km min.  
Operating temperature: -20°C to 70°C

### Application:

Internal wiring of computers, electronic exchanges, measurement control devices, business machines, communication devices and other electronic equipment.



Number	Dimensions			Max. conductor resistance DC 20°C Ω/m	
	TP (mm)	W (mm)	Tolerance		
08	6.35	7.62	±0.30	∅0.100<0.397	
10	8.89	10.16	±0.30		
12	11.43	12.70	±0.30		
14	16.51	17.78	±0.30		
16	19.05	20.32	±0.30		
20	24.13	25.40	±0.30		
24	29.21	30.48	±0.30		
26	31.75	33.02	±0.30		
30	36.83	38.10	±0.30		∅0.127<0.237
34	41.91	43.18	±0.40		
40	49.53	50.80	±0.40		
50	62.23	63.50	±0.40		
60	74.93	76.20	±0.40		
64	80.01	81.28	±0.40		